

# Test certificate

## KASITECH<sup>®</sup> Systematic solutions

KASIGLAS<sup>®</sup> treated with primer Henkel Terostat 8517 H as well as Sika<sup>®</sup> Aktivator 100 and adhesive KASITECH<sup>®</sup> Scheibenfix has passed the tests listed below:

Bead peel test according to DIN 54457 + DIN EN ISO 10365

Cataplasma test according to DIN EN 29142  
7d NK, 7d Cataplasma 70 °C, 1d -20 °C, 3 d NK

condensation water test according to DIN 50017  
7d NK, 7d Condensation water, 3d NK

			7d NK	Cataplasma	Schwitzw.
PC	un-coated	Terostat 8517 H / KASITECH <sup>®</sup> Scheibenfix	1	1	1
PC	coated KASI <sup>®</sup> PC Flex	Terostat 8517 H / KASITECH <sup>®</sup> Scheibenfix	1	1	1
PC	Screen print KASI <sup>®</sup> PC Flex	Terostat 8517 H / KASITECH <sup>®</sup> Scheibenfix	1	1	1

1 (very good) – 4 (inadequate)